

Specification for Models: FW-483-MN, FW-483-A-MN, FW-483-B-MN & FW-483-C-MN  
Friendly® Product – Not ADA Compliant

Warm Rain® model FW-483-MN Friendly® shower fixture is constructed of reinforced polyester resin covered with a high gloss gel-coat of 18 - 20 mils. thickness. The reinforced fiberglass has a minimum content of 18 % fiberglass.

The base is an integral part of the unit.


The unit will measure 48" x 36" x 79" and has a textured bottom floor.

**The Front Outside threshold is 3"**

These units have flat walls and are reinforced for the future installation of grab bars. The reinforcement is shown in the diagram below. See page 2 for options including grab bars & fold-up seat.

Antibacterial additive is an option for this unit.

These Warm Rain® assisted showers arrive on site fully tested, inspected, and certified to meet or exceed the precise standards established by FHA/HUD, materials bulletin 73, American National Standards Z-124.1 and Z-124.2, ASTM/E-84 and is certified by the National Association of Home Builders NAHB). These Adaptable units comply with the Fair Housing Act for Adaptability.



\*\*\*Reinforcement for fold-up seat is only on B & C Packages\*\*\*

Warm Rain® Corporation, P.O. Box 600, Hancock, MI 49930  
Voice: 906-482-3750 Fax: 906-482-2585 E-mail: [tedk@warmrain.com](mailto:tedk@warmrain.com)  
Website: [www.warmrain.com](http://www.warmrain.com)

**FW-483-A-MN: Model includes Grab Bars**

The grab bars will be factory installed. The grab bars will be 1 1/2” outside diameter ADA compliant stainless steel bars. There are 2 - 24” & 1 - 36” horizontal grab bars and 1 – 24” vertical grab bar. The wall reinforcement is wood fiberglassed into the unit. 1 - 24” bar will be placed on both the wet wall and the dry wall 34.5” above the floor. 1 - 36” grab bar will be placed on the back wall 34.5” above the floor. 1 - 24” vertical grab bar will be placed 4” above the horizontal bar half way between the front of the unit and the middle of the wet wall.

**FW-483-B-MN: Model includes Grab Bars & a Fold-up seat**

The grab bars will be factory installed. The grab bars will be 1 1/2” outside diameter ADA compliant stainless steel bars. There are 2 – 24” horizontal grab bars and 1 – 24” vertical grab bar. The wall reinforcement is wood fiberglassed into the unit. 1 - 24” bar will be placed on the wet wall 34.5” above the floor. 1 - 24” grab bar will be placed on the back wall 34.5” above the floor. 1 - 24” vertical grab bar will be placed 4” above the horizontal bar half way between the front of the unit and the middle of the wet wall. The ADA compliant fold-up seat will be factory installed. The seat will support a minimum of 250 #’s. The seat will be placed on the side wall opposite the controls 18” above the floor. The seat shall be a phenolic white ADA compliant seat.

**FW-483-C-MN: Model includes Grab Bars, Fold-up seat, Pressure Balance Valve, Hand held shower with slide bar, Vacuum Breaker, & Curtain rod with brackets**

The grab bars will be factory installed. The grab bars will be 1 1/2” outside diameter ADA compliant stainless steel bars. There are 2 - 24” horizontal grab bars and 1 – 24” vertical grab bar. The wall reinforcement is wood fiberglassed into the unit. 1 - 24” bar will be placed on the wet wall 34.5” above the floor. 1 - 24” grab bar will be placed on the back wall 34.5” above the floor. 1 - 24” vertical grab bar will be placed 4” above the horizontal bar half way between the front of the unit and the middle of the wet wall. The ADA compliant fold-up seat will be factory installed. The seat will support a minimum of 250 #’s. The seat will be placed on the side wall opposite the controls 18” above the floor. The seat shall be a phenolic white ADA compliant seat. 1 - Symmons Temptrol Valve & Kit model # S-25-300-B30-V-X-2000 will include a Temtrol 2000 pressure balance valve, hand held shower with a 30” bar, and a vacuum breaker. Also, 1 - seachrome curtain rod with brackets will be included.



Warm Rain® Corporation, P.O. Box 600, Hancock, MI 49930  
Voice: 906-482-3750 Fax: 906-482-2585 E-mail: [tedk@warmrain.com](mailto:tedk@warmrain.com)  
Website: [www.warmrain.com](http://www.warmrain.com)